Eclipse FlueFire Burners


Parameter Maximum Input per 150mm module, x1000 Btu/h (kW) ¹ For other $\%O_2$ see page 2		Specification with 21% O ₂	Typical Turbine Operating Conditions
		1300 (344)	750 (198)
Minimum Input per 150mm module, x1000 Btu/h (kW) ¹ For other $\%O_2$ see page 2		55-95 (15-25)	75 (20)
Gas Pressure at the burner nozzle, "w.c. (mbar) ⁴	Natural Gas	169 (421)	
	Propane	74 (184)	Natural gas
	Butane	56 (140)	56 (140)
	low calorific gases	depends on specs	
% Process O ₂ upstream		21	15
Process Temperature upstream, °F (°C)		1300 (700)	930 (500)
Process Temperature downstream, °F (°C) ²		1800 (982)	1650 (900)
dP Across Burner, "w.c. (Pa)		0.3-0.5 (75-125)	0.4 (100)
Process Velocity Across the Burner			
TEG Mode, ft/min (m/s)		3800-5000 (19-25)	4000 (20)
FA Mode, ft/min (m/s)		2100-2800 (10-14)	2500 (12.5)
NOx Emissions ³		Consult Eclipse	
CO Emissions ³		Consult Eclipse	
Process Air Distribution Requirements		+/- 15% in velocity across burner	same
Flame Monitoring		UV scanner only	same
Approvals		P	30

- 1. All imperial inputs based upon gross calorific values (HHV). All metric inputs based upon net calorific values (LHV).
- 2. For higher temperatures consult Eclipse.
- 3. Emissions are dependent upon process temperature and oxygen levels.
- 4. Natural gas pressures at high fire (measured at the inlet of the burner manifold) may increase up to 20" w.c. (50 mbar) per 3.3 feet (1 meter) for burners over 3.3 feet (1 meter) in length.

Reference Data					
Fuel Type	MJ/Nm ³	Btu/ft ³	d/sg		
Natural Gas	39	1050	0.6		
Propane	93	2500	1.5		
Butane	123	3300	2.0		



FlueFire Operational Envelope:



Introduction

The Eclipse FlueFire burner was developed by Eclipse for supplementary firing heat turbine exhaust gases using the oxygen present within the exhaust flow to complete the combustion. The high heat release per burner module along with its heat resistent construction will also lend the burner to be applied to other applications requiring large heat inputs and high outlet temperatures.

At oxygen levels below the operating parameters of the burner, a supply duct can be provided to supply combustion air to the burner. Depending on the application, the burner can fire on ratio or with a fixed primary air supply as required for good combustion.

Description

Each burner module consists of a flame stabilizer with two gas nozzles. The stabilization plate is perforated to create a local swirl in the turbine exhaust gas or fresh air. Set into each module are two gas nozzles and one raw gas port. The combination of raw gas ports and nozzles ensures good flame stability over the entire operating range for both turbine exhaust gas and fresh air. The modules are held in place by the gas nozzles such that full thermal expansion is allowed.

Individual burner modules are mounted on a common manifold to form a row. Rows can be fired individually, or provided with flame propagation plates to promote crossignition from one burner row to another. The use of propagation plates accomplishes complete ignition of the burner at a single ignition point, instead of individual ignition points at each burner row. Flame sensing can now be accomplished by a reduced number of flame scanners.

Pilot Burner

The pilot consists of a burner head with ignition plug, located outside the burner duct, and a flame extension tube to overcome the distance between pilot burner head and main burner row. The UV scanner is mounted on the pilot burner head to prove the pilot flame and the main flame after the pilot has been interrupted. A sight glass is provided to observe the pilot flame base only. The pilot assembly includes adjustable gas and air valves in order to obtain the required gas/air ratio and flame length.

Frame

The burner mounting frame is fabricated from heavy construction steel with internal insulation and is suitable for mounting in the duct work between the gas turbine and waste heat boiler. The burner rows are welded on the gas inlet side to the mounting frame. The opposite end is allowed to slide to account for thermal expansion.

Internal insulation consists of 8" thick ceramic fiber covered with a heat resistant cladding designed to allow thermal expansion.

Materials

The burner is completely manufactured from heat resistant materials as specified below:

Gas Manifolds	AISI 136L	(Wst 1.4404)
Stabilization Plate	Aveta 253MA	(Wst 1.4893)
Gas Nozzles	AISI 321	(Wst 1.4541)

